DRY SEPARATION BY DIFFERENCE DENSITY

GSort & GSort GL





GSort GL Highlights

- Direct CAPEX : Specific capacity/investment
- Indirect CAPEX: Cost of installation (two heights available, with and without sunken heavy).
- OPEX: Direct maintenance costs kWh/t*
- Lead time improvements.
- Modularity: Adaptability.

*Metric ton




Parameter/Model	GSort GL	Standard Densimetric Table	
T/h*m width compost 35% humidity	13	6.5	
Compost purity %	99	98	
Compost losses %	2 to 3	3 to 5	
Consumption kw/ton compost	1.75	2.5	
% compost extracted by the filter in a specific case of moisture compost 35%	>40	<25	
Cleaning interval of the treatment bottom	>3 days (sandwich deck)	8h	
Machine downtime for exchanging the Treatment Bottom	5 min	40 min	
Cost reduction in direct investment measured in t/(h*m*EUR) vs standard versions	30%	0	

Advantages of GSort versus standard tables: KPIs




Explore more advantages





OPEX reduction (kWh/t)






Enhanced machine base and increased inclination

GSort GL's cutting-edge design features unique advancements and improvements to the machine inlet, treatment deck design, and air distribution system. These upgrades provide many benefits and provide an optimum sorting experience.





Easy Maintenance

The new air distribution system provides greater flexibility as it's easily adjustable, reducing maintenance time associated with conventional methods.

The treatment bottom can quickly and easily be replaced laterally instead of servicing it through in-/outlet openings.





GSort Highlights

- The GSort model offers improved adaptability to changing inlet properties and processing of materials due to its multiple operating levers in the new design.
- It works well with highly abrasive mineral materials like manganese and provides exceptional purity compared to other market separation equipment.
- ▶ GSort is the leading solution for dry separation, featuring enhanced dimensioning for its vibratory mechanism, suspension frame, and wall.
- Additionally, it has a user-friendly mechanical maintenance design with side openings on the vibratory box.





Fields of Application

GSort GL

Light applications

For fluidization speed < 4 m/s

For densities < 1.7 t/m3 and particle sizes < 35 mm



GSort

Heavy-duty applications

For fluidization speed > 3 m/s

For densities > 1.3 t/m3 and particle sizes > 25 mm

*The fluidization speed is determined by the material's density and the size or particle size distribution.





Models

GSort GL

Table width: 50 cm	GL50
Table width: 100 cm	GL100

Table width: 150 cm

GL50 (Basic)

GL150

GL100 (Basic)

GSort

- G06 Table width: 50 cm
- G13 Table width: 100cm
- G19 Table width: 150 cm

Discover more





Process Robustness & Tolerance

Humidity:

GSort and GSort GL are equipment perfectly capable of working with moisture as long as there is no interparticle adhesiveness and there is a free flow between them.

Feed composition:

GSort and GSort GL provides great stability against feed composition variation.

Granulometry:

The general range of processing between 0.50 and 80 mm fed in optimal factions. On minerals, the range is between 1 and 40 mm fed in optimal fractions.







Industries best suited for

GSort GL

Compost MSW (0 - 10 mm)

Oversized compost MSW (10 - 40 mm)

Glass + organics (0 - 20 mm)

RDF (0-40 mm)

Vermiculite

Anthracite coal

PET-film

Rubber and textile

Fine manganese ore

GSort

Coal

Magnesite

Hematite

Barite

Celestite

Attapulgite

Manganese ore

Ferrum-manganese

Aluminum recycling


Crusted cables

Crusted demolition waste





Success Cases



Watch more videos on 💔



